


## Technical specifications at a glance



### Dimensions of overall length and diameters

	A	B	C	D	E	F	G	H	I	J	K	L
<b>NOBLEX® N6 comfort</b>												
1-6 × 24	30	287	109	-	46	92	34	53	-	179	30	22
<b>NOBLEX® N6</b>												
1-6 × 24	30	287	109	-	46	92	34	53	-	179	30	22
2-12 × 50	56	342	164	60	46	46	34	53	101	133	30	22
2.5-15 × 56	62	362	185	54	46	50	34	53	118	137	30	22
<b>NOBLEX® N5</b>												
1.2-6 × 24	30	274	94	-	46	78	34	55	-	166	30	-
2.4-12 × 50	56	33	149	48	46	45	34	55	87	134	30	-
3-15 × 56	62	356	176	42	46	45	34	55	114	134	30	-
<b>NOBLEX® NZ6 inception</b>												
1-6 × 24	30	282	99	-	46	-	35	59	-	-	30	-
2-12 × 50	56	355	170	37	46	46	35	59	107	140	30	-
3-18 × 56	63	371	188	48	46	56	35	59	114	150	30	-
5-30 × 56	63	410	227	46	46	80	35	59	174	174	30	-

\* The length specifications are measured at zero position of the dioptre adjustment.

1. Connection dimensions filter thread of NOBLEX® N6 comfort 1-6 × 24: M 27 × 0.75
2. Connection dimensions filter thread of NOBLEX® N6 1-6 × 24: M 27 × 0.75
3. Connection dimensions filter thread of NOBLEX® N6 2-12 × 50: M 52 × 0.75
4. Connection dimensions filter thread of NOBLEX® N6 2.5-15 × 56: M 58 × 0.75
5. Connection dimensions filter thread of NOBLEX® N5 1.2-6 × 24: M 27 × 0.75
6. Connection dimensions filter thread of NOBLEX® N5 2.4-12 × 50: M 52 × 0.75
7. Connection dimensions filter thread of NOBLEX® N5 3-15 × 56: M 58 × 0.75
8. Connection dimensions filter thread of NOBLEX® NZ6 1-6 × 24: M 28 × 0.5-6H
9. Connection dimensions filter thread of NOBLEX® NZ6 2-12 × 50: M 55 × 0.75-6H
10. Connection dimensions filter thread of NOBLEX® NZ6 3-18 × 56 and 5-30 × 56: M 61 × 0.75-6H

## Technical specifications at a glance

MODEL	Magnification	Ø Lens aperture (mm)	Ø Exit pupil (mm)	Field of vision (m/100 m)	Field of vision in degrees	Twilight performance	Adjustment per click (cm/100 cm)	Max. adjustment range (cm/100 m)	Dioptre adjustment range (dtp)	Ø Centre tube (mm)	Length at zero position (mm)	Mass without rail (g)	Mass with rail (g)
<b>NOBLEX® N6 comfort</b>													
1-6 × 24	1 × to 6 ×	24	11.1-4.0	37.5-6.25	21.2-3.58	4.9-12	1.0	H: ±185 S: ±185	±3.0	30	287	530	555
<b>NOBLEX® N6</b>													
1-6 × 24	1 × to 6 ×	24	11.1-4.0	37.5-6.25	21.2-3.58	4.9-12	1.0	H: ±185 S: ±185	±3.0	30	287	530	555
2-12 × 50	2 × to 12 ×	50	11.1-4.2	18.75-3.13	10.71-1.79	10-24.5	1.0	H: ±130 S: ±185	±3.0	30	342	660	680
2.5-15 × 56	2.5 × to 15 ×	56	11.1-3.7	15.0-2.5	8.58-1.43	11.8-29	1.0	H: ±100 S: ±60	±3.0	30	362	750	760
<b>NOBLEX® N5</b>													
1.2-6 × 24	1.2 × to 6 ×	24	10.6-4	36.3-6.9	20.57-3.95	5.4-12	10	±240	±3.0	30	274	470	-
2.4-12 × 50	2.4 × to 12 ×	50	10.6-4.2	17.4-3.5	9.94-2.0	11-24.5	10	±120	±3.0	30	330	600	-
3-15 × 56	3 × to 15 ×	56	10.6-3.7	13.8-2.8	7.90-1.60	13-29	10	±100	±3.0	30	356	690	-
<b>NOBLEX® NZ6 inception</b>													
1-6 × 24	1 × to 6 ×	24	9.6-4.0	39.8-6.3	-	5.4-12	1.0	±310	±2.0	30	282	525	-
2-12 × 50	3 × to 18 ×	50	9.6-4.2	19.3-3.1	-	10-24.5	1.0	±140	±2.0	30	355	650	-
3-18 × 56	3 × to 18 ×	56	11.3-3.1	12.6-2.1	-	13-31.7	1.0	±90	±2.0	30	371	790	-
5-30 × 56	5 × to 30 ×	56	11.2-1.8	7.7-1.4	-	16.7-41	1.0	±55	±2.0	30	410	819	-

Subject to technical changes.

- The N5 devices as well as the model N6 1-6 × 24 and all NZ6 models are adjusted to a parallax-free observation distance of 100 m. All other models have a parallax adjustment
- All devices are filled with nitrogen.
- All models with screwed on caps are waterproof. The NZ6 models are waterproof even without screwed caps.
- The middle eye relief of NOBLEX® N5 and N6 is 9.5 cm. With NOBLEX® NZ6 it is on average approx. 9.0 cm.